



3315421606

High definition soc. out., B.3/B.7, ant., matt

Technical properties

Architecture

Number of poles	19pole
-----------------	--------

Connectivity

Outlet	with straight outlet
--------	----------------------

Connectors / jacks	with HDMI double socket, type A, supports HDMI technology (V 2.1)
--------------------	---

Dimensions

Insertion depth	16.8 mm
-----------------	---------

Frequency

Frequency range (vertical)	50...85 Hz
----------------------------	------------

Screen

Resolution	max. 1920 x 1080 px
------------	---------------------

Storage

Transmission rate	max. 8.16 Gbit/s
-------------------	------------------

Materials

Colour of design line	anthracite
-----------------------	------------

Colour	anthracite
--------	------------

RAL colour	RAL 7021 - Black grey
------------	-----------------------

Material	Plastic/metal
----------	---------------

Surface appearance	matt
--------------------	------

Material / surface	gold-plated contacts
--------------------	----------------------

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Identification

Application, usage	Communication technology
--------------------	--------------------------

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7
--------------------------	------------------------------------

Instructions

Information text

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092