



3315426084

## High definition socket outlet Q.x alu velvety, lacquered

### Technical properties

#### Architecture

Number of poles 19pole

#### Connectivity

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

#### Dimensions

Insertion depth 16.8 mm

#### Frequency

Frequency range (vertical) 50...85 Hz

#### Screen

Resolution max. 1920 x 1080 px

#### Storage

Transmission rate max. 8.16 Gbit/s

#### Materials

Colour aluminium

RAL colour RAL 9006 - White aluminium

Material Plastic/metal

Surface appearance velvety

Material / surface gold-plated contacts

#### Installation, mounting

Installation mode without spreader claws

#### Identification

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

#### Instructions

Information text Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092