



3315426086

High definition soc. out., Q.x, ant. velvety, lacq.

Technical properties

Architecture

| | |
|-----------------|--------|
| Number of poles | 19pole |
|-----------------|--------|

Connectivity

| | |
|--------|----------------------|
| Outlet | with straight outlet |
|--------|----------------------|

| | |
|--------------------|---|
| Connectors / jacks | with HDMI double socket, type A, supports HDMI technology (V 2.1) |
|--------------------|---|

Dimensions

| | |
|-----------------|---------|
| Insertion depth | 16.8 mm |
|-----------------|---------|

Frequency

| | |
|----------------------------|------------|
| Frequency range (vertical) | 50...85 Hz |
|----------------------------|------------|

Screen

| | |
|------------|---------------------|
| Resolution | max. 1920 x 1080 px |
|------------|---------------------|

Storage

| | |
|-------------------|------------------|
| Transmission rate | max. 8.16 Gbit/s |
|-------------------|------------------|

Materials

| | |
|-----------------------|------------|
| Colour of design line | anthracite |
|-----------------------|------------|

| | |
|--------|------------|
| Colour | anthracite |
|--------|------------|

| | |
|------------|-----------------------|
| RAL colour | RAL 7021 - Black grey |
|------------|-----------------------|

| | |
|------------------------|-----------|
| Material / workmanship | lacquered |
|------------------------|-----------|

| | |
|----------|---------------|
| Material | Plastic/metal |
|----------|---------------|

| | |
|--------------------|---------|
| Surface appearance | velvety |
|--------------------|---------|

| | |
|--------------------|----------------------|
| Material / surface | gold-plated contacts |
|--------------------|----------------------|

Installation, mounting

| | |
|-------------------|---|
| Installation mode | without spreader claws, for screw fastening |
|-------------------|---|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

Identification

| | |
|--------------------|--------------------------|
| Application, usage | Communication technology |
|--------------------|--------------------------|

| | |
|------------------|------------------------|
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
|------------------|------------------------|

| | |
|--------------------------|--|
| Secondary design line(s) | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |
|--------------------------|--|

Instructions

Information text

Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092