



High definition socket outlet w. 90° plug connection Q.x alu velvety, lacq.

Technical properties

Number of poles	19pole
realiser of poles	1550.0
Connectivity	
Outlet	with straight outlet
Connectors / jacks	with HDMI double socket, type A, supports HDMI technology (V 2.1)
Dimensions	
Insertion depth	41 mm
Frequency	
Frequency range (vertical)	5085 Hz
Screen	
Resolution	max. 1920 x 1080 px
Storage	
Transmission rate	max. 8.16 Gbit/s
Materials	
Colour of design line	aluminium
Surface appearance	velvety
Material / surface	gold-plated contacts
Installation, mounting	
Installation mode	without spreader claws
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Identification	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

Instructions

for compliance with the permissible bending radii,
Art. No. 1068-02 or 9062-74; For the connection of
digital devices for transmission of high-resolution
audio and video signals, such as satellite receivers
and DVD players, to LCD or plasma screens.;
Observe the instructions of the cable and device
manufacturers for maximum HDMI cable lengths!;
Fränkische: "Multimedia tube" for laying preassembled connection cable, Art. no. 294.10.092

Installation recommendation: Kaiser: "Electronic box"

Information text