



3315436086

High definition soc. out. 90° plug connection, Q.x, ant. velvety, lacq.

Technical properties

Architecture

Number of poles	19pole
-----------------	--------

Connectivity

Outlet	with straight outlet
--------	----------------------

Connectors / jacks	with HDMI double socket, type A, supports HDMI technology (V 2.1)
--------------------	---

Dimensions

Insertion depth	41 mm
-----------------	-------

Frequency

Frequency range (vertical)	50...85 Hz
----------------------------	------------

Screen

Resolution	max. 1920 x 1080 px
------------	---------------------

Storage

Transmission rate	max. 8.16 Gbit/s
-------------------	------------------

Materials

Colour of design line	anthracite
-----------------------	------------

Material / workmanship	lacquered
------------------------	-----------

Surface appearance	velvety
--------------------	---------

Material / surface	gold-plated contacts
--------------------	----------------------

Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Identification

Application, usage	Communication technology
--------------------	--------------------------

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---

Instructions

Information text

Installation recommendation: Kaiser: "Electronic box"
for compliance with the permissible bending radii,
Art. No. 1068-02 or 9062-74 ; For the connection of
digital devices for transmission of high-resolution
audio and video signals, such as satellite receivers
and DVD players, to LCD or plasma screens. ;
Observe the instructions of the cable and device
manufacturers for maximum HDMI cable lengths! ;
Fränkische: "Multimedia tube" for laying pre-
assembled connection cable, Art. no. 294.10.092