



3315437009

**High definition soc. out. 90° plug connection, K.1, p. white glossy**

**Technical properties**

**Architecture**

Number of poles 19pole

**Connectivity**

Outlet with straight outlet

Connectors / jacks with HDMI double socket, type A, supports HDMI technology (V 2.1)

**Dimensions**

Insertion depth 41 mm

**Frequency**

Frequency range (vertical) 50...85 Hz

**Screen**

Resolution max. 1920 x 1080 px

**Storage**

Transmission rate max. 8.16 Gbit/s

**Materials**

Colour of design line polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Material / surface gold-plated contacts

**Installation, mounting**

Installation mode without spreader claws, for screw fastening

**Identification**

Application, usage Communication technology

Main design line Berker K.1

**Instructions**

Information text Installation recommendation: Kaiser: "Electronic box" for compliance with the permissible bending radii, Art. No. 1068-02 or 9062-74 ; For the connection of digital devices for transmission of high-resolution audio and video signals, such as satellite receivers and DVD players, to LCD or plasma screens. ; Observe the instructions of the cable and device manufacturers for maximum HDMI cable lengths! ; Fränkische: "Multimedia tube" for laying pre-assembled connection cable, Art. no. 294.10.092