



382210

Switch for blinds 2pole for lock cylinder, blind control

Technical properties

Architecture

Type of control unit Key

Functions

Function with push lock function

Configuration

Switch mode with neutral position

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 40 mm

Height 70.8 mm

Width 70.8 mm

Materials

Surface appearance matt

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Type of connection with screw terminals

Equipment

Closures / Key systems for master-key systems

Use cases

Application Blind control

Identification

Application, usage Blind control

Main design line Blind control