



383120

**Push-b. f.blinds 1p f.lock cylinder, earth contact, splash-prot. flush-mtd IP44**

**Technical properties**

**Architecture**

Type of control unit Key

**Configuration**

Switch mode 1pole

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Momentary-contact current 10 A

**Dimensions**

Depth 40.1 mm

Insertion depth 30.9 mm

Height 70.8 mm

Width 70.8 mm

**Materials**

Material Plastic/metal

**Installation, mounting**

Installation mode without spreader claws, for screw fastening

**Connection**

Type of connection with screw terminals

**Equipment**

Closures / Key systems for master-key systems

**Use cases**

Application Blind control

**Use**

Differentiation characteristic 2 - Sales with earth contact

**Safety**

Protection index IP IP44

---

**Identification**

Main design line

Splash-protected flush-mounted IP44

---

**Instructions**

Information text

Suitable for water-protected, flush-mounted  
installation IP44.