



383120

Push-b. f.blinds 1p f.lock cylinder, earth contact, splash-prot. flush-mtd IP44

Technical properties

Architecture

Type of control unit	Key
----------------------	-----

Configuration

Switch mode	1pole
-------------	-------

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Momentary-contact current	10 A
---------------------------	------

Dimensions

Depth	40.1 mm
Insertion depth	30.9 mm
Height	70.8 mm
Width	70.8 mm

Materials

Material	Plastic/metal
----------	---------------

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

Connection

Type of connection	with screw terminals
--------------------	----------------------

Equipment

Closures / Key systems	for master-key systems
------------------------	------------------------

Use cases

Application	Blind control
-------------	---------------

Use

Differentiation characteristic 2 - Sales	with earth contact
--	--------------------

Safety

Protection index IP	IP44
---------------------	------

Identification	
Main design line	Splash-protected flush-mounted IP44
Instructions	
Information text	Suitable for water-protected, flush-mounted installation IP44.