



383120

Push-b. f.blinds 1p f.lock cylinder, earth contact, splash-prot. flush-mtd IP44

Technical properties

Architecture

Type of control unit	Key
----------------------	-----

Configuration

Switch mode	1pole
-------------	-------

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	250 V AC
---------------	----------

Electric current

Momentary-contact current	10 A
---------------------------	------

Dimensions

Depth	40.1 mm
-------	---------

Insertion depth	30.9 mm
-----------------	---------

Height	70.8 mm
--------	---------

Width	70.8 mm
-------	---------

Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

Connection

Type of connection	with screw terminals
--------------------	----------------------

Equipment

Closures / Key systems	for master-key systems
------------------------	------------------------

Use cases

Application	Blind control
-------------	---------------

Use

Differentiation characteristic 2 - Sales	with earth contact
--	--------------------

Safety

Protection index IP	IP44
---------------------	------

Identification

Main design line	Splash-protected flush-mounted IP44
------------------	-------------------------------------

Information text

Suitable for water-protected, flush-mounted installation IP44.