



390640

**Pullcord switch off/change-over surface-mtd, surface-mtd, white glossy**

**Technical properties**

**Architecture**

Type of control unit pull cord

**Configuration**

Switch mode Off/change-over

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Controls and indicators**

Push-buttons No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

**Dimensions**

Depth 49 mm

Height 61 mm

Width 61 mm

**Length**

Long pullcord 12 cm

**Materials**

Colour independent of design lines white

Colour white

Surface appearance glossy

**Installation, mounting**

Opening knock out opening for entry at top and bottom

Installation mode for wall and ceiling mounting ; for screw fastening

**Connection**

Type of connection with plug-in terminals

Type of connection Quickconnect

**Cable**

Wire

with line and duct entry

**Safety**

---

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | No  |

**Identification**

---

|                    |                                  |
|--------------------|----------------------------------|
| Application, usage | Dry surface-mounted installation |
| Main design line   | Surface-mounted                  |