



390640

Pullcord switch off/change-over surface-mtd, surface-mtd, white glossy

Technical properties

Architecture

Type of control unit pull cord

Configuration

Switch mode Off/change-over

Antibacterial treatment No

Compatibility

IFTTT support available No

Controls and indicators

Push-buttons No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 49 mm

Height 61 mm

Width 61 mm

Length

Long pullcord 12 cm

Materials

Colour independent of design lines white

Colour white

Surface appearance glossy

Installation, mounting

Opening knock out opening for entry at top and bottom

Installation mode for wall and ceiling mounting ; for screw fastening

Connection

Type of connection with plug-in terminals

Type of connection Quickconnect

Cable

Wire

with line and duct entry

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Identification

Application, usage	Dry surface-mounted installation
Main design line	Surface-mounted