



41157004

SCHUKO soc. out., screw-in lift terminals, K.5, stainl. steel, metal matt finish

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line Stainless steel

Material / workmanship metal, matt finish

Surface appearance matt

Metallic colour Yes

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw-in lift terminals

Safety

IK protection code against mechanical impacts 07

| | |
|----------------------------------|-------------------------------------|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |
| Protection | without enhanced contact protection |
| With enhanced contact protection | No |
| Identification | |
| Main design line | Berker K.5 |