



41231606

**SCHUKO soc.out., enhanced contact prot., screw-in lift term., B.3/B.7, ant. matt**

**Technical properties**

**Architecture**

|             |                        |
|-------------|------------------------|
| Design      | according to DIN 49440 |
| Fixing mode | flush-mounting         |

**Configuration**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Frequency       | 50/60 Hz |
| Rated current   | 16 A     |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

**Dimensions**

|                 |       |
|-----------------|-------|
| Insertion depth | 32 mm |
|-----------------|-------|

**Cover, door**

|       |                     |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

**Materials**

|                       |                          |
|-----------------------|--------------------------|
| Colour of design line | anthracite               |
| Colour                | anthracite               |
| Colour                | anthracite charcoal grey |
| RAL colour            | RAL 7021 - Black grey    |
| Material              | thermoplastic            |
| Surface appearance    | matt                     |

**Installation, mounting**

|                   |                     |
|-------------------|---------------------|
| Installation mode | with spreader claws |
|-------------------|---------------------|

**Connection**

|                      |                              |
|----------------------|------------------------------|
| Connection terminals | according to IEC 60884-1     |
| Connection terminals | according to VDE 0620-1      |
| Type of connection   | with screw-in lift terminals |

**Use**

|  |                                |
|--|--------------------------------|
| Differentiation characteristic 2 - Sales | with enhanced touch protection |
| Differentiation characteristic 3 - Sales | with screw-in lift terminals   |

**Safety**

---

|   |                             |
|---|-----------------------------|
| IK protection code against mechanical impacts | 05                          |
| Protection index IP                           | IP20                        |
| Protection                                    | Enhanced contact protection |
| With enhanced contact protection              | Yes                         |

---

**Identification**

---

|                          |                                    |
|--------------------------|------------------------------------|
| Main design line         | Berker S.1/B.3/B.7                 |
| Secondary design line(s) | Berker S.1, Berker B.3, Berker B.7 |

---