



41231909

**SCHUKO soc.out.,enhncd contact prot.,screw-in lift term.,S.1/B.3/B.7,p.wh.**

### Technical properties

#### Architecture

Design according to DIN 49440

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Electric current

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance matt

Metallic colour No

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw-in lift terminals

#### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales with screw-in lift terminals

**Safety**

---

|   |                             |
|---|-----------------------------|
| IK protection code against mechanical impacts | 05                          |
| REACH conform                                 | Yes                         |
| RoHS conform                                  | Yes                         |
| Halogen free                                  | Yes                         |
| Protection                                    | Enhanced contact protection |
| With enhanced contact protection              | Yes                         |

---

**Identification**

---

|                          |                                      |
|--------------------------|--------------------------------------|
| Main design line         | Berker S.1/B.3/B.7                   |
| Secondary design line(s) | Berker S.1 ; Berker B.3 ; Berker B.7 |

---