



41452045

SCHUKO soc.out., mounting orient. var. in 45° steps, screw-in lift term., R.cl, bl.

#### Technical properties

##### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black
Surface appearance	glossy
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with screw-in lift terminals

**Equipment**

---

Type of configuration	Laserdruck
-----------------------	------------

**Use**

---

Differentiation characteristic 2 - Sales	Installation position variable in 45° steps
--	---

---

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

**Safety**

---

Protection index IP	IP20
---------------------	------

---

Protection	without enhanced contact protection
------------	-------------------------------------

---

With enhanced contact protection	No
----------------------------------	----

**Identification**

---

Main design line	Serie R.classic
------------------	-----------------