



41661909

Soc.out. earth. contact US/CAN NEMA 5-15 R, screw term.,S.1,p.white matt plastic

Technical properties

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 15 A

Dimensions

Insertion depth 19 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance matt

Installation, mounting

Installation mode without spreader claws

Connection

Conductor cross-section (rigid) max. 2 x 4 mm²

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw terminals

Standards

Standard NEMA 5-15 R

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection

without enhanced contact protection

Identification

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Information text

Not UL-certified.