



41666084

sock. outl. w. earthing cont. USA/CANADA NEMA 5-15 R, Q.x alu velvety, lacq.

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	125 V
Rated voltage	125 V AC
Frequency	50/60 Hz
Rated current	15 A

##### Dimensions

Insertion depth	19 mm
-----------------	-------

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

##### Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

##### Connection

Type of connection	with screw terminals
--------------------	----------------------

##### Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

##### Standards

Standard	NEMA 5-15 R
----------	-------------

##### Safety

IK protection code against mechanical impacts	02
---	----

Protection

without enhanced contact protection

**Identification**

---

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

**Instructions**

---

Information text

Not UL-certified.