



41666086

**Soc.out. earth.contact US/CAN NEMA 5-15 R, screw term., Q.x, ant.velv.lacq.**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	125 V
Rated voltage	125 V AC
Frequency	50/60 Hz
Rated current	15 A

##### Dimensions

Insertion depth	19 mm
-----------------	-------

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

##### Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

##### Connection

Type of connection	with screw terminals
--------------------	----------------------

##### Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

##### Standards

Standard	NEMA 5-15 R
----------	-------------

##### Safety

IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Protection	without enhanced contact protection
<b>Identification</b>	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
<b>Instructions</b>	
Information text	Not UL-certified.