



41666086

Soc.out. earth.contact US/CAN NEMA 5-15 R, screw term., Q.x, ant.velv.lacq.

Technical properties

Architecture

| | |
|-----------------|----------------|
| Fixing mode | flush-mounting |
| Number of poles | 2pole + earth |

Configuration

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 125 V |
| Rated voltage | 125 V AC |
| Frequency | 50/60 Hz |
| Rated current | 15 A |

Dimensions

| | |
|-----------------|-------|
| Insertion depth | 19 mm |
|-----------------|-------|

Cover, door

| | |
|-------|---------------------|
| Cover | Central cover plate |
|-------|---------------------|

Materials

| | |
|------------------------|--------------------------|
| Colour of design line | anthracite |
| Colour | anthracite |
| Colour | anthracite charcoal grey |
| RAL colour | RAL 7021 - Black grey |
| Material / workmanship | lacquered |
| Material | thermoplastic |
| Surface appearance | velvety |

Installation, mounting

| | |
|-------------------|---|
| Installation mode | without spreader claws, for screw fastening |
|-------------------|---|

Connection

| | |
|--------------------|----------------------|
| Type of connection | with screw terminals |
|--------------------|----------------------|

Use

| | |
|--|----------------------|
| Differentiation characteristic 3 - Sales | with screw terminals |
|--|----------------------|

Standards

| | |
|----------|-------------|
| Standard | NEMA 5-15 R |
|----------|-------------|

Safety

| | |
|---|--|
| IK protection code against mechanical impacts | 05 |
| Protection | without enhanced contact protection |
| Identification | |
| Main design line | Berker Q.1/Q.3/Q.7/Q.9 |
| Secondary design line(s) | Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9 |
| Instructions | |
| Information text | Not UL-certified. |