



41668982

**soc.out. earthing contact USA/CANADA NEMA 5-15 R, screw terminal, S.1, white gl.**

#### Technical properties

##### Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	125 V
Rated voltage	125 V AC
Frequency	50/60 Hz
Rated current	15 A

##### Dimensions

Insertion depth	19 mm
-----------------	-------

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	white
Colour	white
Colour	white
RAL colour	RAL 1013 - Oyster white
Material	thermoplastic

##### Installation, mounting

Installation mode	without spreader claws
-------------------	------------------------

##### Connection

Conductor cross-section (rigid)	4
Type of connection	with screw terminals

##### Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

##### Standards

Standard	NEMA 5-15 R
----------	-------------

##### Safety

IK protection code against mechanical impacts	05
---	----

REACH conform	Yes
RoHS conform	Yes
Protection	without enhanced contact protection
<b>Identification</b>	
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7
<b>Instructions</b>	
Information text	Not UL-certified.