



41668989

**Soc.out. earthing contact USA/CANADA NEMA 5-15 R, screw term., S.1, p.white gl.**

### Technical properties

#### Architecture

Number of poles 2pole + earth

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 15 A

#### Dimensions

Insertion depth 19 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance glossy

#### Installation, mounting

Installation mode without spreader claws

#### Connection

Conductor cross-section (rigid) max. 2 x 4 mm<sup>2</sup>

Type of connection with screw terminals

#### Use

Differentiation characteristic 3 - Sales with screw terminals

#### Standards

Standard NEMA 5-15 R

#### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection

without enhanced contact protection

**Identification**

---

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7

**Instructions**

---

Information text

Not UL-certified.