



41681909

**Soc.out. earth. contact US/CAN NEMA 5-20 R, screw term., S.1, p.white matt lacq.**

### Technical properties

#### Architecture

Number of poles 2pole + earth

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 20 A

#### Dimensions

Insertion depth 19 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Material / workmanship lacquered

Surface appearance matt

#### Installation, mounting

Installation mode without spreader claws ; for screw fastening

#### Connection

Conductor cross-section (rigid) max. 2 x 4 mm<sup>2</sup>

Type of connection with screw terminals

#### Use

Differentiation characteristic 3 - Sales with screw terminals

#### Standards

Standard NEMA 5-20 R

#### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform	Yes
Protection	without enhanced contact protection
<b>Identification</b>	
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7
<b>Instructions</b>	
Information text	Not UL-certified.