



41686084

sock. outl. w. earthing cont. USA/CANADA NEMA 5-20 R, Q.x alu velvety, lacq.

## Technical properties

### Architecture

Number of poles 2pole + earth

### Configuration

Number of modules 1

### Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 20 A

### Dimensions

Insertion depth 19 mm

### Cover, door

Cover Central cover plate

### Materials

Colour of design line aluminium

Material / workmanship lacquered

Surface appearance velvety

### Installation, mounting

Installation mode without spreader claws ; for screw fastening

### Connection

Conductor cross-section (rigid) max. 2 x 4 mm<sup>2</sup>

Type of connection with screw terminals

### Use

Differentiation characteristic 3 - Sales with screw terminals

### Standards

Standard NEMA 5-20 R

### Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection	without enhanced contact protection
<b>Identification</b>	
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
<b>Instructions</b>	
Information text	Not UL-certified.