



41686086

Soc.out. earth. contact US/CAN NEMA 5-20 R, screw term., Q.x, ant.velv.acq.

Technical properties

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 20 A

Dimensions

Insertion depth 19 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance velvety

Installation, mounting

Installation mode without spreader claws ; for screw fastening

Connection

Conductor cross-section (rigid) max. 2 x 4 mm²

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw terminals

Standards

Standard NEMA 5-20 R

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

Identification

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

Instructions

Information text

Not UL-certified.