



41686086

Soc.out. earth. contact US/CAN NEMA 5-20 R, screw term., Q.x, ant.velv.acq.

Technical properties

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	125 V
Rated voltage	125 V AC
Frequency	50/60 Hz
Rated current	20 A

Dimensions

Insertion depth	19 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

Installation, mounting

Installation mode	without spreader claws, for screw fastening
-------------------	---

Connection

Conductor cross-section (rigid)	4
Type of connection	with screw terminals

Use

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

Standards

Standard	NEMA 5-20 R
----------	-------------

Safety

IK protection code against mechanical impacts

05

Protection

without enhanced contact protection

Identification

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

Information text

Not UL-certified.