



41686089

**Soc.out. earth. contact USA/CAN NEMA 5-20 R, screw term., Q.x, p.white velv.**

### Technical properties

#### Architecture

Number of poles 2pole + earth

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 20 A

#### Dimensions

Insertion depth 19 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line polar white

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance velvety

#### Installation, mounting

Installation mode without spreader claws ; for screw fastening

#### Connection

Conductor cross-section (rigid) max. 2 x 4 mm<sup>2</sup>

Type of connection with screw terminals

#### Use

Differentiation characteristic 3 - Sales with screw terminals

#### Standards

Standard NEMA 5-20 R

#### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection

without enhanced contact protection

**Identification**

---

Main design line

Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s)

Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

**Instructions**

---

Information text

Not UL-certified.