



41688982

**soc.out. earthing contact USA/CANADA NEMA 5-20 R, screw terminal, S.1, white gl.**

#### Technical properties

##### Architecture

Number of poles 2pole + earth

##### Configuration

Number of modules 1

##### Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Rated current 20 A

##### Dimensions

Insertion depth 19 mm

##### Cover, door

Cover Central cover plate

##### Materials

Colour of design line white

Colour white

Colour white

Surface appearance glossy

##### Installation, mounting

Installation mode without spreader claws

##### Connection

Conductor cross-section (rigid) max. 2 x 4 mm<sup>2</sup>

Type of connection with screw terminals

##### Use

Differentiation characteristic 3 - Sales with screw terminals

##### Standards

Standard NEMA 5-20 R

##### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection without enhanced contact protection

---

**Identification**

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7

---

**Instructions**

Information text

Not UL-certified.