



41688982

soc.out. earthing contact USA/CANADA NEMA 5-20 R, screw terminal, S.1, white gl.

Technical properties

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 125 V

Rated voltage 125 V AC

Frequency 50/60 Hz

Rated current 20 A

Dimensions

Insertion depth 19 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line white

Colour white

Colour white

Surface appearance glossy

Installation, mounting

Installation mode without spreader claws

Connection

Conductor cross-section (rigid) max. 2 x 4 mm²

Type of connection with screw terminals

Use

Differentiation characteristic 3 - Sales with screw terminals

Standards

Standard NEMA 5-20 R

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection

without enhanced contact protection

Identification

Main design line

Berker S.1/B.3/B.7

Secondary design line(s)

Berker S.1 ; Berker B.3 ; Berker B.7

Instructions

Information text

Not UL-certified.