



4468

**Cable out. low inst. depth, com-tech**

**Technical properties**

**Functions**

Relay space-saving for relays, etc.

**Dimensions**

Insertion depth 23.1 mm

**Materials**

Surface appearance other

**Installation, mounting**

Installation mode low installation depth ; with spreader claws

**Connection**

Terminal without terminal block

**Cable**

Cable clamp with strain relief

Wire for lines Ø max. 9 mm

**Use cases**

Application Communication technology

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Identification**

Application, usage Communication technology

Main design line Accessories

Secondary design line(s) Communication technology ; Serie Glass ; Serie 1930

With imprint No