



4502

Technical properties

Architecture

Fixing mode surface-mounting

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Electric current

Acceptable current rating with AC1 10 A

Dimensions

Depth of installed product 42.5 mm

Length 55 mm

Width of installed product 80 mm

Power supply

Supply voltage 230 V

Lighting control

Brightness measurement range 5 / 1000 Lux

Incandescent bulbs control

Max. power with incandescent lamps 1500 W

Installation, mounting

Mounting type surface-mounted

Connection

Connection cross-sect. flexible conductor 1 / 2,5mm²

Connection cross-sect. rigid cable 1 / 2.5 mm²

Number of contacts 1

Type of contacts 1NC

Safety

Protection index IP IP55

Use conditions

Operating temperature -25...45 °C