



4502

## Technical properties

### Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

### Electric current

Acceptable current rating with AC1	10 A
------------------------------------	------

### Dimensions

Depth of installed product	42.5 mm
Length	55 mm
Width of installed product	80 mm

### Power supply

Supply voltage	230 V
----------------	-------

### Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

### Incandescent bulbs control

Max. power with incandescent lamps	1500 W
------------------------------------	--------

### Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

### Connection

Connection cross-sect. flexible conductor	1 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 2.5 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1NC

### Use conditions

Operating temperature	-25...45 °C
-----------------------	-------------