



4503

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Electric current

Acceptable current rating with AC1	16 A
------------------------------------	------

Dimensions

Depth of installed product	42.5 mm
Length	55 mm
Width of installed product	80 mm

Power supply

Supply voltage	230 V
----------------	-------

Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

Incandescent bulbs control

Max. power with incandescent lamps	3000 W
------------------------------------	--------

Installation, mounting

Mounting type	surface-mounted
---------------	-----------------

Connection

Connection cross-sect. flexible conductor	1 / 2,5mm ²
Connection cross-sect. rigid cable	1 / 2.5 mm ²
Number of contacts	1
Type of contacts	1NC

Safety

Protection index IP	IP55
---------------------	------

Use conditions

Operating temperature	-25...45 °C
-----------------------	-------------