



450502

## Loudspeaker soc. out. High End, com-tech

### Technical properties

#### Connectivity

Outlet	with straight outlet
Connectors / jacks	banana sockets also suitable for screw connection, with 2 metal banana plugs, gold-plated design, with 2 metal banana sockets, gold-plated design

#### Dimensions

Insertion depth	31 mm
-----------------	-------

#### Resistance

Connect transition resistance	< 0.15 mΩ
-------------------------------	-----------

#### Materials

Material	Plastic/metal
----------	---------------

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Conductor cross-section	max. 10 mm <sup>2</sup>
Clamp transition resistance	< 0.1 mΩ

#### Scope of delivery

Component	with 2 metal cable lugs, gold-plated design
-----------	---

#### Safety

Protection index IP	IP20
---------------------	------

#### Identification

Application, usage	Communication technology
Main design line	Communication technology
With imprint	No

#### Instructions

Information text	Recommendation: use deep box for larger cross-sections. Jack and plug with red or black identification ring, as well as a plug connection are suitable for protection low voltage.
------------------	--