



452210

Aerial soc. 3hole single box, DC-permeable, 1930/glass/R.classic

Technical properties

Functions

Function Suitable for HDTV

Connectivity

Connectors / jacks remote supply via F-socket

Reception / transmission for terrestrial reception ; for digital and analogue transmission

Voltage

Voltage DC voltage conducting

Frequency

Broadband technology 5...2400 MHz

Resistance

Wave impedance 75 Ω

Attenuation

Tap loss at 2150 MHz 2 dB

Tap loss at 860 MHz 5.5 dB

Installation, mounting

System for single and distributor SAT systems ; for community, DVB-T and broadband cable systems

Connection

Type of connection with plug-in terminals

Equipment

Supporting plate / Supporting ring external eyelets on the supporting ring can be broken off for round designs

Use

Differentiation characteristic 3 - Sales DC-permeable

Standards

General standards EN 50083-2 and EN 60728-4

Safety

Protective screen according to EN 50083-2, Class A

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature

-25...55 °C

Identification

Application, usage

Communication technology

Main design line

Communication technology