



4538



FCC soc. out., 8-pole, cat.3, com-tech, white

### Technical properties

#### Architecture

Design to according to DIN EN 60603-7

#### Configuration

Category / ports cat.3

#### Compatibility

For registered plugs RJ 11/12/45

#### Connectivity

Outlet with 45° oblique outlet

Plug type for RJ11, RJ12 and RJ45 plugs

#### Main electrical features

Rated voltage 125 V DC

Rated current 1 A

#### Dimensions

Insertion depth 22 mm

#### Frequency

Transmission bandwidth max. 16 MHz

#### Resistance

Transition resistance < 20 mΩ

#### Materials

Colour independent of design lines white

Colour white

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Type of connection with screw terminals

Cat.3 according to DIN EN 50173

Cat.3 to according to TIA/IAE-568-B.2

#### Cable

Conductor Ø max. 1 mm

#### Safety

REACH conform	Yes
RoHS conform	Yes
Protection	No

**Identification**

Application, usage	Communication technology
Main design line	Communication technology