



459410

**Aerial soc. 4hole single box, DC-permeable, 1930/glass/R.classic**

**Technical properties**

**Functions**

Function Suitable for HDTV

**Connectivity**

Connectors / jacks remote supply via F-sockets

Outputs with 2 independent SAT outputs (F-sleeves) and 2 IEC outputs (male/female)

Reception / transmission for terrestrial reception ; for digital and analogue transmission

**Voltage**

Voltage DC voltage conducting

**Frequency**

Broadband technology 5...2400 MHz

**Resistance**

Wave impedance 75 Ω

**Attenuation**

Tap loss at 2150 MHz 2 dB

Tap loss at 860 MHz 2 dB

**Installation, mounting**

System for community and broadband cable systems ; for single and distributor SAT systems ; for multi-switch systems

**Connection**

Type of connection with screw terminals

Connection for simultaneous connection of radio and TV receiver as well as 2 independent SAT receivers

**Settings**

Programs also to add SAT programmes in broadband cable systems

**Equipment**

Supporting plate / Supporting ring external eyelets on the supporting ring can be broken off for round designs

**Use**

Differentiation characteristic 3 - Sales DC-permeable

**Standards**

**Safety**

---

Protective screen	(VHF/UHF) according to EN 50083-2, Class B ; (SAT) according to EN 50083-2, Class A
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

---

Operating temperature	-25...55 °C
-----------------------	-------------

**Identification**

---

Application, usage	Communication technology
Main design line	Communication technology