



459410

Aerial soc. 4hole single box, DC-permeable, 1930/glass/R.classic

Technical properties

Function	Suitable for HDTV
runction	Sultable for horv
Connectivity	
Connectors / jacks	remote supply via F-sockets
Outputs	with 2 independent SAT outputs (F-sleeves) and 2 IEC outputs (male/female)
Reception / transmission	for terrestrial reception ; for digital and analogue transmission
Voltage	
Voltage	DC voltage conducting
Frequency	
Broadband technology	52400 MHz
Resistance	
Wave impedence	75 Ω
Attenuation	
Tap loss at 2150 MHz	2 dB
Tap loss at 860 MHz	2 dB
Installation, mounting	
	for community and broadband cable systems ; for
System	single and distributor SAT systems ; for multi-switch systems
Connection	
Type of connection	with screw terminals
Connection	for simultaneous connection of radio and TV receiver as well as 2 independent SAT receivers
Settings	
Programs	also to add SAT programmes in broadband cable systems
Equipment	
Supporting plate / Supporting ring	external eyelets on the supporting ring can be broken off for round designs
Use	
Differentiation characteristic 3 - Sales	DC-permeable

Safety

Protective screen	(VHF/UHF) according to EN 50083-2, Class B ; (SAT) according to EN 50083-2, Class A
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-2555 °C
Identification	
Application, usage	Communication technology
Main design line	Communication technology