



4604

Built-in soc. for floating output, Accessories

Technical properties

Dimensions

Insertion depth 35.3 mm

Materials

Surface appearance other

Connection

Conductor cross-section (rigid) max. 6 mm²

Connection pins according to DIN 42801

Scope of delivery

Component with a green yellow signal ring

Equipment

Centre plates / central plates for centre plate with cut-out dia. 18.8 mm

Safety

REACH conform Yes

RoHS conform Yes

Identification

Application, usage Connecting systems and accessories

Main design line Accessories

Secondary design line(s) ACCESSORIES ; Berker B.3 ; Berker S.1 ; Berker B.7 ; Berker Arsys ; Berker K.5 ; Berker K.1 ; Module inserts