



47157003

## Schuko socket outlet with screw-in lift terminals K.5 aluminium anodised

### Technical properties

#### Architecture

Design according to DIN 49440

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Electric current

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

Installation depth, flush-mounted boxes 31 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line Aluminium

Material / workmanship aluminium, anodised

Surface appearance matt

Metallic colour Yes

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

#### Safety

IK protection code against mechanical impacts 07

REACH conform Yes

RoHS conform Yes

---

Halogen free Yes

Protection without enhanced contact protection

---

**Identification**

Main design line Berker K.5