



47157115

SCHUKO soc. out. "EDV" imprint, K.1, red glossy

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 16 A

Electric current

Rated current 16 A

Cover, door

Cover Central cover plate

Materials

Design lines special colours red

Surface appearance glossy

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Safety

IK protection code against mechanical impacts 05

RoHS conform Yes

Halogen free No

Protection without enhanced contact protection

With enhanced contact protection No

Identification

Main design line Berker K.1

Instructions

Information text Insert colour-coded.