



47231909

**SCHUKO soc. out., enhncd contact prot., S.1/B.3/B.7, p. white, matt, plastic**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Equipment**

**Use**

---

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

**Safety**

---

IK protection code against mechanical impacts	05
---	----

---

Protection index IP	IP20
---------------------	------

---

Protection	Enhanced contact protection
------------	-----------------------------

---

With enhanced contact protection	Yes
----------------------------------	-----

**Identification**

---

Main design line	Berker S.1/B.3/B.7
------------------	--------------------

---

Secondary design line(s)	Berker S.1, Berker B.3, Berker B.7
--------------------------	------------------------------------