



47272045

SCHUKO soc. out. 45°, R.1/R.3, black glossy

Technical properties

Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Electric current

Rated current	16 A
---------------	------

Dimensions

Insertion depth	32 mm
-----------------	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of labelling	217,217,217
Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

Installation, mounting

Entries	for diagonal insertion
Installation mode	with spreader claws

Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

Settings

Shading parameter	R1_czarny
Laser parameter	R1_schwarz
Equipment	
Type of configuration	Laserdruck
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No
Identification	
Main design line	Berker R.1/R.3/R.8
Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8
Instructions	
Information text	Specially suited for combining several socket outlets if right angle plugs are used.