



47278982

SCHUKO soc. out. 45°, S.1, white glossy

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line white

Colour white

Colour white

Surface appearance glossy

Installation, mounting

Entries for diagonal insertion

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Safety

IK protection code against mechanical impacts 02

REACH conform Yes

RoHS conform Yes

Halogen free	Yes
Protection	without enhanced contact protection
With enhanced contact protection	No
Identification	
Main design line	Berker S.1/B.3/B.7
Secondary design line(s)	Berker S.1 ; Berker B.3 ; Berker B.7
Instructions	
Information text	Specially suited for combining several socket outlets if right angle plugs are used.