



47287106

**SCHUKO soc. out. 45°, K.1, ant. matt, lacq.**

### Technical properties

#### Architecture

Design according to DIN 49440

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

#### Electric current

Rated current 16 A

#### Dimensions

Insertion depth 32 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance matt

#### Installation, mounting

Entries for diagonal insertion

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

#### Use

Differentiation characteristic 1 - Sales with labelling field

#### Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No

---

**Identification**

Main design line	Berker K.1
------------------	------------

---

**Instructions**

Information text	Specially suited to combinations of several socket outlets if right angle plugs are used. 1140. Labelling field height designed for 6 mm P-touch strips.
------------------	--