



47357003

**SCHUKO soc. out., enhncd contact prot., K.5, al., al. anodised**

**Technical properties**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	Aluminium
Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	aluminium, anodised
Material	Aluminium
Surface appearance	matt
Metallic colour	Yes

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales

with enhanced touch protection

**Safety**

IK protection code against mechanical impacts

07

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

**Identification**

Main design line

Berker K.5