



47357006

**SCHUKO soc. out., enhncd contact prot., K.1, ant. matt, lacq.**

#### Technical properties

##### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales

with enhanced touch protection

**Safety**

IK protection code against mechanical impacts

05

Protection index IP

IP20

Protection

Enhanced contact protection

With enhanced contact protection

Yes

**Identification**

Main design line

Berker K.1