



47397003

**SCHUKO soc. out., K.5, al., matt, lacq.**

#### Technical properties

##### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

##### Configuration

Number of modules	1
-------------------	---

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

##### Electric current

Rated current	16 A
---------------	------

##### Dimensions

Insertion depth	32 mm
-----------------	-------

##### Cover, door

Cover	Central cover plate
-------	---------------------

##### Materials

Colour	aluminium
Colour	aluminium optics
RAL colour	RAL 9006 - White aluminium
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	matt

##### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

##### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

##### Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

**Safety**

---

IK protection code against mechanical impacts 05

Protection index IP IP20

Protection without enhanced contact protection

With enhanced contact protection No

**Identification**

---

Main design line Berker K.5

**Instructions**

---

Information text Labelling field height arranged for P-touch strips 6 mm.