



47397006

SCHUKO soc. out., K.1, ant. matt, lacq.

Technical properties

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line anthracite

Material / workmanship lacquered

Surface appearance matt

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Use

Differentiation characteristic 1 - Sales with labelling field

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

| | |
|----------------------------------|-------------------------------------|
| Halogen free | No |
| Protection | without enhanced contact protection |
| With enhanced contact protection | No |

Identification

| | |
|------------------|------------|
| Main design line | Berker K.1 |
|------------------|------------|

Instructions

| | |
|------------------|----------------------------------------------------------|
| Information text | Labelling field height arranged for P-touch strips 6 mm. |
|------------------|----------------------------------------------------------|