



47397113

SCHUKO soc. out. "SV" imprint, K.1, green glossy

## Technical properties

### Architecture

Design	according to DIN 49440
Fixing mode	flush-mounting

### Configuration

Number of modules	1
-------------------	---

### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

### Electric current

Rated current	16 A
---------------	------

### Dimensions

Insertion depth	32 mm
-----------------	-------

### Cover, door

Cover	Central cover plate
-------	---------------------

### Materials

Design lines special colours	green
Colour	green
Colour	green
RAL colour	RAL 6029 - Mint green
Material	thermoplastic

### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

### Connection

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

### Use

Differentiation characteristic 1 - Sales	Labelling field
--	-----------------

### Safety

IK protection code against mechanical impacts	05
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection
With enhanced contact protection	No

#### Identification

Main design line	Berker K.1
------------------	------------

#### Instructions

Information text	Insert colour-coded. ; Labelling field height arranged for P-touch strips 6 mm.
------------------	---